

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [64325-1010](#)  
**Status:** **Active**  
**Overview:** CMC Sealed, Hybrid, Modular Connectors and Headers  
**Description:** CMC Blind Plug for cavity 0.635mm

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification AS-64318-002 (PDF)</a>
<a href="#">Product Specification PS-64318-001 (PDF)</a>	<a href="#">Application Specification AS-64318-002-FR (PDF)</a>
<a href="#">Product Specification PS-64319-002 (PDF)</a>	<a href="#">Application Specification AS-64319-002 (PDF)</a>
<a href="#">Product Specification PS-64321-001 (PDF)</a>	<a href="#">Application Specification AS-64319-002-CN (PDF)</a>
<a href="#">Product Specification PS-64326-001 (PDF)</a>	<a href="#">Application Specification AS-64319-002-FR (PDF)</a>
<a href="#">Application Specification AS-500993-002 (PDF)</a>	<a href="#">Packaging Specification PK-64325-001 (PDF)</a>
<a href="#">Application Specification AS-501820-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification AS-501820-001-JP (PDF)</a>	

**General**

Product Family	Crimp Housings
Series	<a href="#">64325</a>
Application	Signal
Comments	For additional details please refer to Application Tooling Specification.. Secures sealing system when flexibility is required for unused cavities with standard backplate
Overview	<a href="#">CMC Sealed, Hybrid, Modular Connectors and Headers</a>
Product Name	CMC

**Physical**

Circuits (maximum)	0
Circuits Detail	N/A
Color - Resin	White
Gender	Plug
Glow-Wire Compliant	No
Keying to Mating Part	N/A
Lock to Mating Part	No
Material - Resin	Nylon
Number of Rows	0
Packaging Type	Carton
Panel Mount	No
Pitch - Mating Interface	N/A
Pitch - Termination Interface	N/A
Polarized to Mating Part	N/A
Stackable	No
Temperature Range - Operating	-40°C to +125°C

**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-500993-002, AS-501820-001, AS-501820-001-JP, AS-64318-002, AS-64318-002-FR, AS-64319-002, AS-64319-002-CN, AS-64319-002-FR
Packaging Specification	PK-64325-001
Product Specification	PS-64318-001, PS-64319-002, PS-64321-001, PS-64326-001, RPS-500993-001
Sales Drawing	SD-64325-001




image - Reference only

**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No**  
**Low-Halogen Status Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[64325Series](#)

**Mates With**

CMC Connector [64318](#) , [64319](#) , [64320](#) , [64321](#) , [64326](#)

**Use With**

CMC Connector [64318](#) , [64319](#) , [64320](#) , [64321](#) , [64326](#)

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**