

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [19418-0040](#)  
**Status:** **Active**  
**Overview:** MX150L™ Sealed Connector System  
**Description:** MX150L™ 16 Circuit Receptacle for 18-22 AWG Wire, without CPA

**Documents:**

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)  
[Product Specification PS-19417-001 \(PDF\)](#)

**Agency Certification**

CSA LR18689  
 UL E152602

**General**

Product Family Crimp Housings  
 Series [19418](#)  
 Application Power, Wire-to-Board, Wire-to-Wire  
 Overview [MX150L™ Sealed Connector System](#)  
 Product Literature Order No 987650-2181  
 Product Name MX150L™

**Physical**

Circuits (maximum) 16  
 Flammability 94V-0  
 Gender Female  
 Glow-Wire Compliant No  
 Lock to Mating Part Yes  
 Number of Rows 2  
 Packaging Type Bag  
 Panel Mount No  
 Pitch - Mating Interface 5.84mm  
 Polarized to Mating Part Yes  
 Stackable No  
 Temperature Range - Operating -40°C to +125°C

**Electrical**


Current - Maximum per Contact 18A

**Material Info**

UPC 822348526505

**Reference - Drawing Numbers**

Product Specification PS-19417-001  
 Sales Drawing SD-19418-007



*image - Reference only*

**EU RoHS**

**ELV and RoHS Compliant**

**REACH SVHC**

Not Reviewed

**Low-Halogen Status**

**Not Reviewed**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

19418Series

**Mates With**

19419 , 19429

**Use With**

19420 Female Crimp Terminal