

CLULITE 1W LED Head Torches



- High intensity long life LEDs (1W - 15 times brighter than standard LEDs)
- Ultra low power consumption
- Adjustable through 90° to focus on work area
- 4 mode operation
- Shock-resistant rubber
- Rubber seal for maximum water-resistance
- Fully sealed switch
- Supplied with adjustable head strap with padded front section and 3 x AA batteries
- Rechargeable version supplied with adjustable head strap with padded front section, battery pack and mains charger



	101-3171	101-3172
LED Life	100,000 hours	100,000 hours
Battery Life:		
100% brightness	3 hours	4 hours
50% brightness	10 hours	9 hours
25% brightness	24 hours	16 hours
Flashing mode	7 hours	7 hours
Dims (Torch Head - L x Dia)	50 x 45mm	50 x 45mm
Weight (inc batteries)	195g	228g

416741.406143

Description	Order Code	Price Each
Head Torch	101-3171	
Rechargeable Head Torch	101-3172	