

Products

Product On-Line Catalog

[Product Search](#)

Evaluate

- [FAQ's](#)

Design a Solution

- [Part Draw ings](#)

- [PDF-Adhesive Bac ..](#)

How to Buy

- [Bill of Material](#)

- [Favorite Products List](#)

- [Locate Distributor](#)

[Home](#) > [Product On-Line Catalog](#) > [Product Search](#) >

Current refinements (click to remove) Search Tips 

[Part Number](#) > **ABMM-AT-D0**

Your search criteria matched only one product, shown below

ABMM-AT-D0



- Superior adhesive for long term reliability
 - 2-up mount configuration speeds liner removal and installation
 - 4-way cable tie entry makes part orientation fast and easy
 - Adhesive backing allows routing of wires and cables where mounting holes cannot be drilled
 - Use with Panduit cable ties for a complete wire routing solution
- ‡ Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, H = Heavy, HLM = Miniature Tak-Ty® Hook & Loop Cable Ties.

▪ Part Number	ABMM-AT-D0
▪ RoHS Compliancy Status	Compliant
▪ Part Description	4-Way Adhesive Backed Cable Tie Mount
▪ Product Type	Cable Tie Mounts - Adhesive Backed
▪ Material	Weather Resistant ABS
▪ Color	Black
▪ UL Recognized	E136577
▪ Height (In.)	0.18
▪ Height (mm)	4.6
▪ Length (In.)	0.75
▪ Length (mm)	19.1
▪ Width (In.)	0.75
▪ Width (mm)	19.1
▪ Adhesive Type	Acrylic
▪ CE Compliant	Yes
▪ Environment	Outdoor/High Temp
▪ Max. Bundle Diameter (mm)	3.7
▪ Max. Continuous Use Temperature	180°F (82°C)
▪ Max. Static Load (g)	136
▪ Max. Static Load (Lbs.)	0.30
▪ Mounting Method	Acrylic Adhesive Tape
▪ Pricing Description	Cable Tie Mount, Hi Tmp. Adh., .75"x.75" (19.1mm x 19.1mm), WR BL
▪ Temperature Range	180°F (82°C)
▪ Type	Adhesive Backed
▪ Used With Cable Ties	M, I
▪ Min. Order UOM	PC
▪ Min. Order Qty.	500
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.