

Products

Product On-Line Catalog
[Product Search](#)

Evaluate

- [FAQ's](#)

Design a Solution

- [Catalog Cut Sheet](#)
- [PDF-CLT25F-C3 Pr](#)
- [PDF-CLT25F-C3 Pr](#)
- [Part Drawings](#)
- [PDF-Corrugated L ..](#)

How to Buy

- [Bill of Material](#)
- [Favorite Products List](#)
- [Locate Distributor](#)

[Home](#) > [Product On-Line Catalog](#) > [Product Search](#) >

Current refinements (click to remove) [Search Tips](#)

[Part Number](#) > **CLTS25F-C**

Your search criteria matched only one product, shown below

CLTS25F-C



Corrugated Loom Tubing is offered for applications where spiral wrap or braided expandable sleeving may be difficult to install or where they do not offer the amount of protection required.

- Protects and reduces the risk of damage to wiring
- Crush impact and abrasion resistant
- Hold in place with push type cable ties adhesive or push type mounts
- Bundle wires in control panels
- Contain and organize loose and bundled wiring harnesses

‡Reel packaging may contain splices.

* Order number of reels required.

Contact Panduit Customer Service for additional sizes, materials, colors and bulk packaging options.

- [Part Number](#)
- [RoHS Compliancy Status](#)
- [Part Description](#)

CLTS25F-C

Compliant

Solid Corrugated Loom Tubing is offered for applications where Spiral Wrap or Braided Expandable Sleeving may be difficult to install or they do not offer the amount of protection required.

- [Product Type](#)
- [Material](#)
- [Color](#)
- [CE Compliant](#)
- [Flammability Rating](#)
- [Ft. Per Pkg.](#)
- [Inside Diameter \(In.\)](#)
- [Inside Diameter \(mm\)](#)
- [Length Per Reel \(ft.\)](#)
- [Length Per Reel \(m\)](#)
- [Outside Diameter \(In.\)](#)
- [Outside Diameter \(mm\)](#)
- [Pricing Description](#)
- [Temperature Range](#)
- [Type](#)
- [Min. Order UOM](#)
- [Min. Order Qty.](#)
- [BOM Qty. \(# of Pkgs.\)](#)

Solid Wall Corrugated Loom Tubing

Polyethylene

Black

No

HB

100

0.28

7.0

100

30.5

0.40

10.1

Corr. Loom Tubing Solid, .25" (6.4mm) x 100', Black

-40°F – 122°F (-40°C – 50°C)

Solid Wall Corrugated Loom Tubing

RL

1

- [Add to Favorite Product List](#)

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.