




# 97 22 240 Crimping Pliers



## Technical details

<b>No.</b>	97 22 240	
<b>EAN</b>	4003773070726	
<b>Pliers</b>	black lacquered	
<b>Handles</b>	with multi-component grips	
<b>Capacity</b>	0,75 - 6,00	mm <sup>2</sup>
<b>AWG</b>	18 - 10	
<b>Applications</b>	insulated terminals and plug connectors	
<b>Number of crimping positions</b>	3	
 <b>Net weight</b>	300	g
 <b>Gross weight</b>	300	g
 <b>Length</b>	240	mm

## Description

- for cutting cables, stripping wire and crimping insulated and non-insulated terminals, connectors and plug type connectors
- with threaded holes for cutting copper and brass screws threaded M 2.6 / 3.0 / 3.5 / 4.0 and 5.0 mm
- Special steel, high-strength

## Applications

