







BitBuddy 29, TORX®, 8-pcs.


Housing:	Box of impact resistant, glass-fibre reinforced polyamide - permanently robust. Bit clamping element with push buttons, 180° rotation. Extra folding element for the magnetic bit holder.
Bits:	31-series MaxxTor bits.
Geometry:	Maximum length torsion zone individually matched to the profile. Precision-milled profile for perfect fit and maximum performance.
Holder:	
Application:	Compact bit box with the most common bits. Ideal for frequently varying fastening applications within one work sector. Push the Wiha logo slightly, and the bits are ready to be inserted into the bit holder! Plug & Work & Store - Maximum efficiency due to direct bit insertion without any problems. Insert, work, store.
Extra:	Design tried and tested a million times Always ready to use - easily fits into trouser pockets or the belt clip.

Ord.No.	
36920	5

Ord.No.	Quantity					
01895	1	1/4	1/4	58		
36822	1				T10	29
36823	1				T15	29
36824	2				T20	29
36825	1				T25	29
36826	1				T30	29
36827	1				T40	29