

Twist drills DIN 338 type N HSS-TiN



Ø mm	Total length mm	Flute length mm	Article no. HSS-TiN	Price each €	Ø mm	Total length mm	Flute length mm	Article no. HSS-TiN	Price each €
1,00	34,0	12,0	250 010 TX		7,00	109,0	69,0	250 070 TX	
1,50	40,0	18,0	250 015 TX		7,50	109,0	69,0	250 075 TX	
2,00	49,0	24,0	250 020 TX		8,00	117,0	75,0	250 080 TX	
2,50	57,0	30,0	250 025 TX		8,50	117,0	75,0	250 085 TX	
3,00	61,0	33,0	250 030 TX		9,00	125,0	81,0	250 090 TX	
3,30	65,0	36,0	250 033 TX		9,50	125,0	81,0	250 095 TX	
3,50	70,0	39,0	250 035 TX		10,00	133,0	87,0	250 100 TX	
4,00	75,0	43,0	250 040 TX		10,20	133,0	87,0	250 102 TX	
4,20	75,0	43,0	250 042 TX		10,50	133,0	87,0	250 105 TX	
4,50	80,0	47,0	250 045 TX		11,00	142,0	94,0	250 110 TX	
5,00	86,0	52,0	250 050 TX		11,50	142,0	94,0	250 115 TX	
5,50	93,0	57,0	250 055 TX		12,00	151,0	101,0	250 120 TX	
6,00	93,0	57,0	250 060 TX		12,20	151,0	101,0	250 122 TX	
6,50	101,0	63,0	250 065 TX		12,50	151,0	101,0	250 125 TX	
6,80	109,0	69,0	250 068 TX		13,00	151,0	101,0	250 130 TX	

Twist drill sets DIN 338 type N HSS-TiN ground in steel case

19-piece set of twist drills DIN 338 HSS-TiN
Ø 1,0 mm up to 10,0 mm in increments 0,5 mm

Art. no. A 250 214 T

Packing unit = 25 pcs.

25-piece set of twist drills DIN 338 HSS-TiN
Ø 1,0 mm up to 13,0 mm in increments 0,5 mm

Art. no. A 250 215 T

Packing unit = 20 pcs.

