



Speed, Performance, Value - The Right Balance

- Selectable readability for different environments
- 360° rotational hook
- Large red LED display
- Remote control for easy operation
- Rechargeable battery for up to 150 hours of usage
- Robust metal die cast housing
- Colour coded, sealed keypad
- Easy access to the rechargeable battery
- External calibration
- Full range tare
- Simple user-friendly operation
- Weighing



Technical Specifications

Model	IHS 1	IHS 3	IHS 5	IHS 10
Maximum capacity	1000kg	3000kg	5000kg	10000kg
Readability	200g	500g	1kg	2kg
Repeatability (S.D.)	200g	500g	1000g	2000g
Linearity (\pm)	200g	500g	1000g	2000g

General Specifications

Typical stabilisation time	3 Sec
Units of measurement	Kilogram (kg)
Power supply	7.2VDC 2Amp adapter and internal rechargeable battery
Display	30mm LED



Adam Equipment - offices worldwide

www.adamequipment.com