



INCAP11E

BRIGHT

- White LED provides 40 lumens in high mode



VERSATILE

- 3 light modes – high and low white for general lighting and red for preserving night vision
- Clip attaches to both caps and helmets



HANDY

- Light swivels 360° for pinpoint positioning
- Separate buttons for white and red modes



WEATHERPROOF

- The light still operates after exposure to splashing water from any direction
- Stands up to rough weather



Weatherproof and sturdy, Energizer® Industrial™ 360° Cap Light is a versatile solution for hands-free lighting both indoors and out. Its clip attaches securely to both caps and helmets and the unique swivel base allows 360° rotation. Variable lighting sources provide the right brightness for any job – high and low white for general illumination or red for preserving night vision. In addition, discrete switching allows red and white LEDs to operate independently.




Before Using Your Flashlight:
Please read all instructions and cautionary markings on the package and light

Product Detail:

Designation:	Energizer Industrial 360° LED Cap Light
Model:	INCAP11E
Color:	Yellow and Black
Power Source:	One "AA"
ANSI/NEDA:	Series 24
Lamp:	One White LED, One Red LED
Lamp Life (hr):	Lifetime
Lamp Output (lumens):	High - 40, Low - 13
Beam Distance (m):	High - 30, Low - 19, Red - 6
Peak Beam Intensity (cd):	High - 225, Low - 90, Red - 10
Run Time (h:mm):	High - 4, Low - 22, Red - 41 with Energizer Max batteries
Typical Weight:	61.4 grams with alkaline "AA" battery
Dimensions (mm):	50 x 70 x 39

Performance:



Tested according to ANSI/NEMA FL 1 Standards.

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication
Contents herein do not constitute a warranty
©Energizer / All Rights Reserved