


Standard D-Sub



Item #	Description	1-9	10-24	25-99	100-249	250-499
✓RoHS DGB9F	Slim-Line Gender Changer/Adapters - Reduce Port Receptacle Strain Up To 90% Slim-Line Gender Changer, DB9 Female / Female	4.95	4.46	3.96	3.46	2.97
DGB9M	Slim-Line Gender Changer, DB9 Male / Male	4.95	4.46	3.96	3.46	2.97
DGB15F	Slim-Line Gender Changer, DB15 Female / Female	5.95	5.36	4.76	4.17	3.57
DGB15M	Slim-Line Gender Changer, DB15 Male / Male	5.95	5.36	4.76	4.17	3.57
DGB25F	Slim-Line Gender Changer, DB25 Female / Female	6.95	6.25	5.56	4.87	4.17
DGB25M	Slim-Line Gender Changer, DB25 Male / Male	6.95	6.25	5.56	4.87	4.17
DGB37F	Slim-Line Gender Changer, DB37 Female / Female	8.95	8.05	7.16	6.26	5.37
DGB37M	Slim-Line Gender Changer, DB37 Male / Male	8.95	8.05	7.16	6.26	5.37
DGB50F	Slim-Line Gender Changer, DB50 Female / Female	10.95	9.86	8.76	7.66	6.57
DGB50M	Slim-Line Gender Changer, DB50 Male / Male	10.95	9.86	8.76	7.66	6.57

✓RoHS Socket Saver Adapters - Extend D-Sub Connector Usage and Avoid Major Repairs

DGB9MF	Slim-Line Socket Saver, DB9 Male / Female	4.95	4.46	3.96	3.46	2.97
DGB15MF	Slim-Line Socket Saver, DB15 Male / Female	5.95	5.36	4.76	4.17	3.57
DGB25MF	Slim-Line Socket Saver, DB25 Male / Female	6.95	6.25	5.56	4.87	4.17
DGB37MF	Slim-Line Socket Saver, DB37 Male / Female	8.95	8.05	7.16	6.26	5.37
DGB50MF	Slim-Line Socket Saver, DB50 Male / Female	10.95	9.86	8.76	7.66	6.57

High-Density D-Sub



✓RoHS High-Density Slim-Line Gender Changers - Same Small Size for High-Density D-Subs

DGBH15F	Slim-Line Gender Changer, HD15 Female / Female	7.95	7.16	6.36	5.56	4.77
DGBH15M	Slim-Line Gender Changer, HD15 Male / Male	7.95	7.16	6.36	5.56	4.77
DGBH26F	Slim-Line Gender Changer, HD26 Female / Female	8.95	8.05	7.16	6.26	5.37
DGBH26M	Slim-Line Gender Changer, HD26 Male / Male	8.95	8.05	7.16	6.26	5.37
DGBH44F	Slim-Line Gender Changer, HD44 Female / Female	9.95	8.96	7.96	6.96	5.97
DGBH44M	Slim-Line Gender Changer, HD44 Male / Male	9.95	8.96	7.96	6.96	5.97
DGBH62F	Slim-Line Gender Changer, HD62 Female / Female	12.95	11.65	10.36	9.06	7.77
DGBH62M	Slim-Line Gender Changer, HD62 Male / Male	12.95	11.65	10.36	9.06	7.77
DGBH78F	Slim-Line Gender Changer, HD78 Female / Female	13.95	12.55	11.16	9.76	8.37
DGBH78M	Slim-Line Gender Changer, HD78 Male / Male	13.95	12.55	11.16	9.76	8.37

✓RoHS High-Density Socket Saver Adapters - Great for Preventing Wear on High-Density Connectors

DGBH15MF	Slim-Line Socket Saver, HD15 Male / Female	7.95	7.16	6.36	5.56	4.77
DGBH26MF	Slim-Line Socket Saver, HD26 Male / Female	8.95	8.05	7.16	6.26	5.37
DGBH44MF	Slim-Line Socket Saver, HD44 Male / Female	9.95	8.96	7.96	6.96	5.97
DGBH62MF	Slim-Line Socket Saver, HD62 Male / Female	12.95	11.65	10.36	9.06	7.77
DGBH78MF	Slim-Line Socket Saver, HD78 Male / Female	13.95	12.55	11.16	9.76	8.37

✓RoHS Slim-Line Gender Changer/Adapters - with Pin 9 Missing for Legacy VGA Cable Applications

DGBV15F	Slim-Line Gender Changer, HD15 Female / Female	7.95	7.16	6.36	5.56	4.77
DGBV15M	Slim-Line Gender Changer, HD15 Male / Male	7.95	7.16	6.36	5.56	4.77
DGBV15MF	Slim-Line Socket Saver, HD15 Male / Female	7.95	7.16	6.36	5.56	4.77
DMA100MM	PS-2 Monitor Adapter, DB9 Male / HD15 Male	7.55	6.80	6.04	5.28	4.53

✓RoHS Slim-Line Gender Changers and Socket Saver - Typical Centronic 36 and SCSI/Telco 50

DGC36F	Slim-Line Centronic Gender Changer, 36 Pin Female / Female	9.65	8.69	7.72	6.75	5.79
DGC36M	Slim-Line Centronic Gender Changer, 36 Pin Male / Male	9.65	8.69	7.72	6.75	5.79
DGC50F	Slim-Line SCSI Gender Changer, 50 Pin Female / Female	10.95	9.86	8.76	7.66	6.57
DGC50M	Slim-Line SCSI Gender Changer, 50 Pin Male / Male	10.95	9.86	8.76	7.66	6.57
DGC50MF	Slim-Line SCSI Socket Saver, 50 Pin Male / Female	10.95	9.86	8.76	7.66	6.57





✓RoHS D-Sub Gender Changer Assortment Kit - Never Have a Mismatched Data Cable Again

Always have the right gendered cable when making equipment changes out in the field. Each of these assortment kits have a total of 8 adapters for just about every D-Sub cable correction. DGB1010K includes: DB9, DB15, DB25 and DB37; the DGBH1010K high-density kit includes DGBH15, DGBH26, DGBH44 and DGBH62, each in male/male and female/female versions. The total price of these kits is less than the total cost of individual gender changers. These slimline gender changers are all shielded construction and are extremely compact. These kits are a must for every technician. Packaged in a high impact seven compartment carry box.

DGB1010K	Slim-Line Gender Changer Kit, 8 Pieces	49.95	44.96	39.96	34.96	29.97
DGBH1010K	Hi-Density Gender Changer Kit, 8 Pieces	69.95	62.96	55.96	48.96	41.97

✓RoHS Slim-Line Loopback Test Plugs - Emulate Working Conditions for Your Testing Needs

DMA019S	Slim-Line Parallel Loopback Plug, DB25 Male	6.95	6.25	5.56	4.87	4.17
DMA021T	Slim-Line Loopback Plug, DB9 Female	6.95	6.25	5.56	4.87	4.17



Easily panel mount adapters  **Online Video**
L-com.com/Videos/A03

STEP 1

1. Remove standard hardware provided with adapter. Mount adapter from rear of panel.

STEP 2

2. Secure with jackscrew SDG450XS (purchased separately) from the front of the panel.

STEP 3

3. Thread hex nut SDHS (purchased separately) onto exposed threads of SDG450XS.

*** Note: .062" (0.2cm) Max. panel thickness**

*** Note: Maximum recommended panel thickness is 0.062" (0.2cm). Dimensions in excess of 0.062" (0.2cm) can limit proper cable mating due to hex nut protrusion. Panels exceeding 0.062" (0.2cm) can be milled down to the recommended thickness in the area around the adapter.**

"We order quite a bit from L-com and have always been very pleased with the product selection and service that you offer. We really appreciate the fast response to any questions we have. L-com is reliable and easy to work with. Keep up the excellent work!" - Iain Jenkins, Nexjen Systems