

Immersion Heater Controllers

FST17A SupplyMaster 7 Day Fused Spur Timeswitch



Shares all the features and benefits of the FST11A above, plus weekday/weekend (5-2) or individual day (7) programming.

Four ON/OFF programmes are available and if selected to operate over all 7 days, 28 On & OFF switchings per week will result.

- Up to 28 ON and OFF programmes per week.
- Permanent OFF and timed outputs available.
- Easy view 24 hour digital clock/timer display.
- Optional 1 or 2 hour boost facility.
- Automatic Summer/Winter time changeover.
- Self-cancelling override.
- Shortest switching time 1 minute.
- Programme advance and review options.
- BS1362 fuse replaceable from front.
- Double pole switch for ease of control.
- Integral memory back up battery retains programmes in event of power failure.
- Fits a single gang wall box min. 25mm deep.
- **Part No. FST17A**

Specification

Timer Mode	7 Day
Setting Type	Digital
Operating Voltage	230V AC
Switch Rating 230V AC	13A Resistive (3kW)
Operating Temperature	-10 to 40°C
Conforms to Directives	73/23/EEC, 89/336/EEC
Dimensions (mm)	Width 85, Height 85, Depth 38