

## ≡ JOKAB SAFETY ≡

|                |  |
|----------------|--|
| Article number | 20-057-00                                  |
| Description    | C5 Cable with shield 5x0,34mm <sup>2</sup> |
| Specification  | UL2464 22AWG                               |

|      |                        |
|------|------------------------|
| Size | 22 tinned copper (AWG) |
|------|------------------------|

|                |                                 |
|----------------|---------------------------------|
| Insulation     | PVC (RoHS)                      |
| Outer diameter | 1,3±0,10mm                      |
| Color          | Brown, White, Blue, Black, Grey |

|                  |            |
|------------------|------------|
| Outer insulation | PVC (RoHS) |
| Outer diameter   | 5,5mm      |
| Color            | Black      |

|                 |                  |
|-----------------|------------------|
| Rated Voltage   | 300 V            |
| Rated Temp.     | 80 ° C           |
| Conductor Res.  | 60,25 Ω/KM 20° C |
| Insulation Res. | 2,5 Ω/KM 25° C   |

|                |  |
|----------------|--|
| Article number | 20-057-10                                  |
| Description    | C8 Cable with shield 8x0,34mm <sup>2</sup> |
| Specification  | UL2464 22AWG                               |

|      |                        |
|------|------------------------|
| Size | 22 tinned copper (AWG) |
|------|------------------------|

|                |  |
|----------------|--|
| Insulation     | PVC (RoHS)   |
| Outer diameter | 1,3±0,10mm   |
| Color          | White, Brown, Green, Yellow, Grey, Pink, Blue, Red |

|                  |            |
|------------------|------------|
| Outer insulation | PVC (RoHS) |
| Outer diameter   | 6,3mm      |
| Color            | Black      |

|                 |                  |
|-----------------|------------------|
| Rated Voltage   | 300 V            |
| Rated Temp.     | 80 ° C           |
| Conductor Res.  | 60,25 Ω/KM 20° C |
| Insulation Res. | 2,5 Ω/KM 25° C   |

# ≡ JOKAB SAFETY ≡

|                |   |  |
|----------------|---|--|
| Article number | 20-057-15   |  |
| Description    | C9 Cable with shield 7x0,51 + 2x0,82mm <sup>2</sup> |  |
| Specification  | UL2464 7x20AWG + 2x18AWG                            |  |

|                |  |                   |
|----------------|--|-------------------|
| Size           | 20 AWG tinned cu.                            | 18 AWG tinned Cu. |
| Insulation     | PVC (RoHS)                                   | PVC (RoHS)        |
| Outer diameter | 1,5±0,10mm                                   | 1,9±0,10mm        |
| Color          | White, Green, Yellow, Grey, Pink, Red, Black | Brown, Blue       |

|                  |            |  |
|------------------|------------|--|
| Outer insulation | PVC (RoHS) |  |
| Outer diameter   | 8±0,30 mm  |  |
| Color            | Black      |  |

|                 |                  |                  |
|-----------------|------------------|------------------|
| Rated Voltage   | 300 V            |                  |
| Rated Temp.     | 80 ° C           |                  |
| Conductor Res.  | 40,40 Ω/KM 20° C | 30,38 Ω/KM 20° C |
| Insulation Res. | 2,5 Ω/KM 20° C   | 2,5 Ω/KM 20° C   |

|                |   |  |
|----------------|---|--|
| Article number | 20-057-20   |  |
| Description    | C13 Cable w. shield 11x0,51 + 2x0,82mm <sup>2</sup> |  |
| Specification  | UL2464 11x20AWG + 2x18AWG                           |  |

|                |  |                   |
|----------------|--|-------------------|
| Size           | 20 AWG tinned cu.  | 18 AWG tinned Cu. |
| Insulation     | PVC (RoHS)   | PVC (RoHS)        |
| Outer diameter | 1,5±0,10mm   | 1,9±0,10mm        |
| Color          | White, Green, Yellow, Grey, Pink, Red, Black, Purple, Grey+Pink, Red+Blue, White+Green | Brown, Blue       |

|                  |            |  |
|------------------|------------|--|
| Outer insulation | PVC (RoHS) |  |
| Outer diameter   | 9±0,30mm   |  |
| Color            | Black      |  |

|                 |                  |                  |
|-----------------|------------------|------------------|
| Rated Voltage   | 300 V            |                  |
| Rated Temp.     | 80 ° C           |                  |
| Conductor Res.  | 40,40 Ω/KM 20° C | 30,38 Ω/KM 20° C |
| Insulation Res. | 2,5 Ω/KM 20° C   | 2,5 Ω/KM 20° C   |