

6.02116.50 BS 18 Li

18 Volt Cordless Drill/Screwdriver BS 18



- Variospeed (V) electronics for infinitely variable speed change
- Quick stop for rapid fastening of screws
- Integrated working light for good vision even in dark corners
- Multifunctional monitoring system to protect the machine and battery pack
- Robust battery packs with capacity display for checking the charge status
- 3 year battery pack warranty

Comparative technical values

Type of battery pack	Li-ion
Battery pack voltage	18 V
Capacity of battery pack	1,5 Ah
Maximum torque, soft	24 Nm
Maximum torque, hard	48 Nm
Adjustable torque	0,8 - 5 Nm
- Drill diameter in	
- Steel	10 mm
- Wood	20 mm
Idle revolutions	0 - 450 / 0 - 1.650 /min
Drill spindle thread	1/2 " - 20 UNF
Chuck adapter	1 - 10 mm
Weight (including battery pack)	1,53 kg

Scope of delivery

2 Li-Power Compact battery packs (18 V/1.5 Ah), Charger SC 60 Plus, Plastic carry case