



by Schneider Electric

List Price \$35.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

### Technical Characteristics

Ampere Rating (Resistive)	10A (30Vdc)
Ampere Rating (General Use)	10A (28Vdc)
RoHS Compliant	Yes
Contact Material	Silver Tin Oxide
Approvals	UL Listed (with 8501NR socket) - UL Recognized Component - CSA Certified - CE Marked
Operating Times	Pick-Up: 25ms(max) Drop-Out: 20ms(max)
Operating Temperature Range	-40°F to 158°F
Relay Type	Miniature - Standard
Coil Voltage	24Vdc
Manual Operator	No
Type	R
Pilot Light	No
Snapmount Socket	8501NR42
Horsepower Rating	n/a
Mounting Type	Socket
Type of Pins	Spade
Contact Arrangement	DPDT

### Shipping and Ordering

Category	21143 - Relays, Miniature, Plug-in, Type R
Discount Schedule	CP2
GTIN	00785901131366
Package Quantity	1
Weight	0.09 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	CN

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.