

8538SBG12V02SCombination Starter Fusible Disconnect Class H
(30A), Size: 0, NEMA 1, 3-Pole

List Price \$1,344.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.****Technical Characteristics**

Thermal Units Required	3
Phase	3-Phase
Pilot Light	None
External Reset	Yes
Action	Non-Reversing
Type	S
Auxiliary Contacts	None
Control Source	Separate Control Circuit
Control Units	None
Disconnect Type	Fusible Disconnect Switch
Enclosure Type	General Purpose (Indoor)
Enclosure Rating	NEMA 1
Fuse Clip Amperes	30A
Fuse Type	Class H
Horsepower Rating (1-Phase)	Not Rated
Maximum Voltage Rating	600 Vac
Horsepower Rating (3-Phase)	3HP@200/230Vac
Mounting Type	Surface
NEMA Size	0
Number of Poles	3-Pole
Operating Voltage	120Vac@60Hz - 110Vac@50Hz
Overload Type	Thermal - Melting Alloy
Weight	38 lbs

Shipping and Ordering

Category	21212 - Starters, Combination, NEMA, Enclosed (NEMA 1 & 12), Size 0
Discount Schedule	CP1
GTIN	00785901748182
Package Quantity	1
Weight	34.92 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y

Generated: 08/06/2012 07:03:14

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.