



by Schneider Electric

List Price \$1,144.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

Technical Characteristics

Application	General Purpose - Intended for power, heating and lighting applications
Approvals	cULus Listed
Enclosure Code	10A
Enclosure Material	Painted Steel
Enclosure Rating	NEMA 3R
Enclosure Type	Rainproof and Ice/Sleet proof (Indoor/Outdoor)
Insulation Temperature	180 Degrees C
Mounting Type	Wall
Phase	1-Phase
Primary	240 x 480VAC
Rating	3kVA
Secondary	120/240VAC
Specifications	Sealed and Resin Filled
Full Capacity Taps	None
Temperature Rise	115 Degrees C
Type	Dry
Weathershield	Not required for outdoor use
Depth	6.50 Inches
Height	10.50 Inches
Width	8.62 Inches

Shipping and Ordering

Category	16277 -
Discount Schedule	PE2
GTIN	00785901359418
Package Quantity	1
Weight	59.78 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	MX

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.