

# 8910DPA43V14

Definite Purpose Contactor (Type: DPA) 40A,  
3-Pole, 3-Phase, Non-Reversing



by Schneider Electric

List Price \$88.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

## Technical Characteristics

Maximum Voltage Rating	600VAC
Mounting Type	Panel
Number of Poles	3-Pole
Ampere Rating	40A
Approvals	UL Recognized - CSA Certified - CE Marked
Enclosure Type	Open
Horsepower Rating (1-Phase)	3HP@115VAC - 7.5HP@230VAC
Horsepower Rating (3-Phase)	10HP@230VAC - 20HP@460/575VAC
Locked Rotor Amperes	240A@230VAC - 200A@460VAC - 160A@575VAC
Phase	3-Phase
Operating Voltage	24VAC@50/60Hz
Action	Non-Reversing
Type	DPA

## Shipping and Ordering

Category	21344 - Contactors, Definite Purpose, 40 Amp
Discount Schedule	CP1B
GTIN	00785901073451
Package Quantity	1
Weight	1.19 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	CN

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.