



List Price \$255.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

### Technical Characteristics

Total Travel	90°
Operating Torque/Force	4 Inch-Pounds
Basic Switch (Plug-In Unit)	Standard
Actuator	Lever Arm (ordered separately)
Turret Head	Rotary Head (for Type C Lever Arms)
Plug-In Receptacle	Standard
Actuation	CW and CCW
Actuator Action	Spring Return - Standard Pretravel
Differential Travel	4°
Pre-Travel	10°
Approvals	UL Listed - CSA Certified - CE Marked
Body Material	Zinc Alloy
Connection Type	0.5 Inch NPT Conduit Entrance (screw clamp terminals)
Contact Operation	Snap Action
Contact Rating	NEMA A600/R300
Contact Material	Silver Alloy
Contact Configuration	2 NO/2 NC
Contact Form	Form ZZ - DPDT-DB
Pilot Light	None
Ampere Rating	10A
Maximum Voltage Rating	600V
Type	C
Operating Temperature Range	-20°F to 185°F
Type of Duty	Heavy Duty

### Shipping and Ordering

Category	21499 - Limit Switches, Heavy Duty, Type C
Discount Schedule	DS1
GTIN	00785901500650
Package Quantity	10
Weight	1.25 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y

Generated: 08/06/2012 07:24:49

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.