



List Price \$38.60 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

Technical Characteristics

Approvals	UL File Number E42259 CCN NKCR - CSA File Number LR24590 Class 3211-03 - CE Marked
Bezel Material	Black Plastic
Button/Cap Color	Universal (Contains 1 of each: Black, Red, Green, Yellow, Orange, Blue and White)
Button Type	Standard Pushbutton
Guard Type	Extended Guard (Black Plastic)
Contact Configuration	No Contact Blocks
Enclosure Type	Water tight, Dust tight, Oil tight and Corrosion Resistant (Indoor/Outdoor)
Enclosure Rating	NEMA 1/2/3/3R/4/4X/6/12/13
Head Type	Round
Light Module Supply Voltage	n/a
Light Module Type	n/a
Markings	None
Maximum Voltage Rating	600V
Mounting Type	Panel
Number of Operators	1
Number of Positions	2
Operator Action	Momentary
Size	30mm
Operator Type	Non-Illuminated
Type	K

Shipping and Ordering

Category	21429 - Push Buttons, Corrosion Resistant, Type SK & SKY
Discount Schedule	CS1
GTIN	00785901524380
Package Quantity	1
Weight	0.11 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	MX

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.

Generated: 08/06/2012 07:24:28