



List Price \$7.80 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

### Technical Characteristics

|                        |  |
|------------------------|--|
| Net Weight             | 0.56 oz  |
| Color                  | Gray   |
| Standard Package Size  | 50   |
| Fuse Size              | 5 x 20mm or 5 x 25mm fuse  |
| Maximum Voltage Rating | 600V   |
| Mounting Type          | Rail (35mm DIN 3)  |
| Terminal Type          | Screw Clamp  |
| Block Type             | Fused Disconnect   |
| Type                   | AB1  |
| Wire Size              | #22 to #10 AWG (Cu)  |
| Ampere Rating          | 15A  |
| Depth                  | 2.15 Inches  |
| Height                 | 3.04 Inches  |
| Approvals              | UL Recognized File: E164359 CCN XCFR2 - CSA Certified File: 702070 Class 6228 01 - CE Marked |
| Width                  | 0.31 Inches  |

### Shipping and Ordering

|                   |   |
|-------------------|---|
| Category          | 21715 - Blocks, Terminal, IEC, Channel Mount, Type AB1                  |
| Discount Schedule | CP5   |
| GTIN              | 00785901580003  |
| Package Quantity  | 50  |
| Weight            | 0.04 lbs.   |
| Availability Code | Stock Item: This item is normally stocked in our distribution facility. |
| Returnability     | Y   |
| Country of Origin | DE  |

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.