



List Price \$6.20 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

### Technical Characteristics

Net Weight	0.88 oz
Color	Green/Yellow
Standard Package Size	100
Maximum Voltage Rating	600V
Mounting Type	Rail (35mm DIN 3)
Number of Points	2
Terminal Type	Screw Clamp
Block Type	Grounding
Type	AB1
Wire Size	#22 to #10 AWG (Cu)
Depth	1.91 Inches
Height	2.01 Inches
Approvals	UL Recognized File: E164359 CCN XCFR2 - CSA Certified File: 702070 Class 6228 01 - CE Marked
Width	0.24 Inches

### Shipping and Ordering

Category	21715 - Blocks, Terminal, IEC, Channel Mount, Type AB1
Discount Schedule	CP5
GTIN	00785901369868
Package Quantity	100
Weight	0.06 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	DE

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.