

CA2KN22F7

CONTROL RELAY 600VAC 10AMP IEC +OPTIONS

List Price \$35.50 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

Technical Characteristics

Ampere Rating	10A
Approvals	UL Listed File Number: 164353 CCN NKCR - CSA Certified File Number: LR43364 Class: 3211 03 - CE Marked
Marketing Trade Name	TeSys
Contact Configuration	2 NO - 2 NC
Voltage Code	F7
Coil Voltage	110VAC
Integral Suppression Device	No
Mounting Type	Din Rail(35mm)/Panel
Terminal Type	Screw Clamp
Type	TeSys K
Depth	2.24 Inches
Height	2.28 Inches
Width	1.77 Inches
Weight	0.40 Pounds

Shipping and Ordering

Category	22371 - Relays, Control, IEC
Discount Schedule	I12
GTIN	00785901898740
Package Quantity	1
Weight	0.4 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	FR

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.