

9012GAW5K1

PRESSURE SWITCH 480VAC 10AMP G +OPTIONS

List Price \$422.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

Technical Characteristics

Electrical Connection	1/2" 14 NPT
Switch Type	Single Stage
Enclosure Rating	NEMA 4/4X/13
Differential Type	Adjustable
Differential	6.0 to 30 PSIG
Pressure Range on Decreasing	3.0 to 150 PSIG
Fluid Connection	1/4" 18 NPTF (internal)
Actuator Type	Diaphragm (Low Pressure)
Range Scale Window	Yes
Flange Material	Zinc Plated Steel
External Range Adjustment	Slotted for Screwdriver
Diaphragm Material	Nitrile (Buna-N)
Maximum Allowable Pressure	475 PSIG
Contact Arrangement	SPDT (isolated)
Pilot Light	None
Locking	None
Enclosure Type	Water tight, Dust tight, Oil tight and Corrosion Resistant (Indoor/Outdoor)
Fluid Characteristics	Hydraulic Oils, Air, Non-Corrosive Liquids and Non-Corrosive Gas
Maximum Voltage Rating	600V
Ambient Temperature Range	-10° to 185°F (-23° to 85°C)
Continuous Current Rating	10A
Media Temperature Range	-40° to 250°F (-40° to 120°C)
Shock Resistance	50 g
Operating Cycles/Min	120 operating cycles per minute (max)
Drift	+/- 1% of the adjustable range over 1 million operations
Repeat Accuracy	+/- 0.1 to 1%
Conformity to Standards	UL 508, CSA 3211-03, IEC 60957.5.1, CE
RoHS	No
Certifications	UL Listed and CSA Certified as industrial control equipment

Shipping and Ordering

Category	21522 - Pressure Switches, Machine Tool & Industrial, Control Circuit Rated, Type G,
Discount Schedule	DS1
GTIN	00785901047735
Package Quantity	1
Weight	3.16 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	MX

Generated: 08/06/2012 07:25:39

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.

Generated: 08/06/2012 07:25:39