

List Price \$224.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.****Technical Characteristics**

Horsepower Rating (1-Phase)	1.5HP@115VAC - 3HP@230VAC
Maximum Voltage Rating	600VAC
Mounting Type	Panel
Number of Poles	3-Pole
Starter Type	Non-Reversing
Thermal Trip Setting	17A to 23A
Type	GV2
Horsepower Rating (3-Phase)	5HP@200VAC - 7.5HP@230VAC - 15HP@460VAC - 20HP@575VAC
Marketing Trade Name	TeSys
Operator Type	Pushbutton
Overload Type	Ambient Compensated Bimetallic (Class 10)
Interrupt Rating	Standard
Terminal Type	Screw Clamp
Approvals	UL Listed File Number: E164864 NLRV - CSA Certified File Number: LR81630 Class: 3211 05 - CE Marked

Shipping and Ordering

Category	22367 - Protectors, Starter, Manual, Type GV2
Discount Schedule	I11
GTIN	00785901212010
Package Quantity	1
Weight	0.65 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	FR

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.