

List Price \$41.50 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

### Technical Characteristics

Auxiliary Contacts	3 N.O./1 N.C.
Ampere Rating	10A
Application	Instantaneous Auxiliary
Certifications	UL Listed (E164862 / NLDX) - CSA Certified (LR43364 3211 04) - IEC Rated (60647-4) - CE Marked - RoHS Compliant
Marketing Trade Name	TeSys
Maximum Voltage Rating	600 Vac
Mounting Style	Clip-On (Front)
Terminal Type	Screw Clamp
Type	TeSys D

**Notes:**

For low consumption coils, only one front-mounted two-contact block allowed. No side-mounted contact blocks allowed.

### Shipping and Ordering

Category	22341 - Contactors, IEC, Accessories, D, K & F-Line
Discount Schedule	I12
GTIN	00785901213710
Package Quantity	1
Weight	0.14 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	FR

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.