

List Price \$149.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.****Technical Characteristics**

Certifications	UL Listed (E164862 / NLDX) - CSA Certified (LR43364 3211 04) - IEC Rated (60647-4) - CE Marked - RoHS Compliant
Contacteur Type	Non-Reversing
Inductive Amperes (AC3)	12A
Resistive Amperes (AC1)	25A
Horsepower Rating (1-Phase)	1HP@115Vac - 2HP@230Vac
Horsepower Rating (3-Phase)	3HP@200/230Vac - 7.5HP@460Vac - 10HP@575Vac
Marketing Trade Name	TeSys
Number of Poles	3-Pole (3 NO)
Maximum Voltage Rating	600 Vac
Mounting Style	35mm DIN Rail
Coil Voltage Code	BD
Coil Consumption Sealed	5.4 W
Coil Voltage	24Vdc
Coil Consumption Inrush	5.4 W
Weight	0.72 lbs (0.325 kg)
Power Wire Size	#10 to #18 AWG
Control Terminal Torque	15 lb-in (1.7 Nm)
Power Terminal Torque	15 lb-in (1.7 Nm)
Terminal Type	Screw Clamp
Control Wire Size	#10 to #18 AWG
Type	TeSys D

Shipping and Ordering

Category	22345 -
Discount Schedule	I12
GTIN	00785901207245
Package Quantity	1
Weight	1.15 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	FR

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.