

List Price \$172.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.****Technical Characteristics**

Contacteur Type	Non-Reversing
Inductive Amperes (AC3)	32A
Resistive Amperes (AC1)	50A
Certifications	UL Listed (E164862 / NLDX) - CSA Certified (LR43364 3211 04) - IEC Rated (60647-4) - CE Marked - RoHS Compliant
Maximum Voltage Rating	600 Vac
Marketing Trade Name	TeSys
Horsepower Rating (1-Phase)	2HP@115Vac - 5HP@230Vac
Horsepower Rating (3-Phase)	10HP@200/230Vac - 20HP@460Vac - 30HP@575Vac
Number of Poles	3-Pole (3 NO)
Coil Voltage	24Vac@50/60Hz
Mounting Style	35mm DIN Rail
Coil Consumption Sealed	7.5 VA
Terminal Type	Screw Clamp
Coil Voltage Code	B7
Coil Consumption Inrush	70 VA
Power Wire Size	#6 to #14 AWG
Control Terminal Torque	15 lb-in (1.7 Nm)
Weight	0.83 lbs (0.375 kg)
Power Terminal Torque	20 lb-in (2.5 Nm)
Type	TeSys D
Control Wire Size	#10 to #18 AWG

Shipping and Ordering

Category	22345 -
Discount Schedule	I12
GTIN	00785901207184
Package Quantity	1
Weight	0.91 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	FR

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.