

# LUB12

## Motor Starter Power Base (TeSys U)

### Non-Reversing, 12A



List Price \$246.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

### Technical Characteristics

|                             |   |
|-----------------------------|---|
| Control Connection          | Screw Clamp Terminals                           |
| Power Connection            | Screw Clamp Terminals                           |
| Self Protected              | Yes   |
| Ampere Rating               | 12A   |
| Horsepower Rating (1-Phase) | 0.5HP@115VAC - 2HP@230VAC                       |
| Horsepower Rating (3-Phase) | 3HP@200/230VAC - 7.5HP@460VAC - 10HP@575/600VAC |
| Marketing Trade Name        | TeSys   |
| Type                        | TeSys U   |
| Operating Voltage           | Determined by Control Unit Selection            |
| Weight                      | 1.98 Pounds                                     |
| Action                      | Non-Reversing                                   |
| Terminal Type               | Screw Clamp                                     |

### Shipping and Ordering

|                   |   |
|-------------------|---|
| Category          | 22396 -   |
| Discount Schedule | I11   |
| GTIN              | 00785901222248  |
| Package Quantity  | 1   |
| Weight            | 1.86 lbs.   |
| Availability Code | Stock Item: This item is normally stocked in our distribution facility. |
| Returnability     | Y   |
| Country of Origin | FR  |

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.