

List Price \$72.60 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.****Technical Characteristics**

|                        |   |
|------------------------|---|
| Ampere Rating          | 5A  |
| Enclosure Type         | Water tight, Dust tight and Corrosion Resistant (Indoor/Outdoor)                                    |
| Approvals              | UL Listed File Number E164353 CCN NKCR - CSA Certified File Number LR44087 Class 321103 - CE Marked |
| Bezel Material         | Plastic   |
| Button/Cap Color       | Red   |
| Button Type            | Mushroom (30mm)   |
| Contact Configuration  | 1 NO - 1 NC   |
| Maximum Voltage Rating | 240VAC  |
| Mounting Type          | Panel   |
| Size                   | 16mm  |
| Terminal Type          | Quick Connect   |
| Operator Action        | Maintained - Turn-to-Release  |
| Utilization Category   | AC15 - DC13   |
| Operator Type          | Non-Illuminated   |
| Type                   | XB6   |
| Enclosure Rating       | NEMA 4/4X/12  |
| Head Type              | Round   |

**Shipping and Ordering**

|                   |   |
|-------------------|---|
| Category          | 22459 - Push Buttons, Plastic, 16mm, IEC, Type XB6                      |
| Discount Schedule | CS2   |
| GTIN              | 00785901146247  |
| Package Quantity  | 1   |
| Weight            | 0.05 lbs.   |
| Availability Code | Stock Item: This item is normally stocked in our distribution facility. |
| Returnability     | Y   |
| Country of Origin | MX  |

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.