





# P2664 Series



## Specifications



|                       |       |                                |
|-----------------------|-------|--------------------------------|
| Plunger               | ..... | Hardened BeCu                  |
| Body                  | ..... | Gold-plated phosphorous bronze |
| Spring                | ..... | Stainless steel                |
| Ball                  | ..... | Stainless steel                |
| Electrical Resistance | ..... | <10mΩ                          |
| Maximum Current       | ..... | 5 amps                         |
| Working Travel        | ..... | .084" (2.13)                   |

| Spring Force in oz. (grams) | Initial  | Working   |
|-----------------------------|----------|-----------|
| Standard:                   | 2.0 (57) | 3.6 (102) |
| Alternate:                  | 3.0 (85) | 5.7 (162) |




## Pogo® Receptacle


The P2664 Series is designed to be used with the PR541 Series receptacles below. The recommended mounting hole is .069 (1.75mm). The recommended drill is 1.75mm. Use ARIT54 tool for installation.



### PR541-0 Crimp




### PR541-0F (Flush Mount)




### PR541-1 Solder

#### PR541-1F (Flush Mount)



### PR541-2 Wire Wrap

#### PR541-2F (Flush Mount)



### PR541-3 Round Post

#### PR541-3F (Flush Mount)

