



# Sta-Kon®

**Disconnects**

**T&B Catalog Number:**

RAS18-250AX

**UPC Number:**

78621007075

**Status:**

Active

**Description:**

Heat-Shrinkable Polyolefin Female - 250 Series Disconnects For Wire Range 22-18 Length 1.82, Tab Size .250 x .032 , Red

**WEB\_USE**

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

**Features**

Unique construction of the female disconnect offers long-term dependability. Brazed seam serrated barrel provides maximum tensile strength.

**General**

|                 |                            |
|-----------------|----------------------------|
| Disconnect Type | Female - 250 Series        |
| Insulation Type | Heat-Shrinkable Polyolefin |
| Terminal Series | RAS                        |
| Material        | Brass                      |
| Finish          | Electro -Tin Plated        |
| Color           | Red                        |
| Wire Range      | 22-18                      |
| Tab Size        | .250 x .032                |

**Dimension Information**

|                             |      |
|-----------------------------|------|
| Maximum Insulation (inches) | .170 |
| A (inches)                  | 1.82 |

**Specifications**

|                     |           |
|---------------------|-----------|
| Temperature Rating  | 150°C     |
| Voltage Rating      | 600V      |
| Flammability Rating | UL 94 V-0 |

**Tooling**

|                   |                      |
|-------------------|----------------------|
| Tool Charts       | Available on Website |
| Application Tools | WT1255               |
| Recommended Tool  | ERG4255              |

**Packaging**

|                    |                  |
|--------------------|------------------|
| T&B Order Multiple | 25               |
| T&B Inner Pack     | 25               |
| Package in Units   | 250              |
| Package Type       | Standard         |
| T&B Sold in UOM    | Each             |
| T&B Weight Per UOM | 0.8 lbs. per 100 |

**Application Support**

|                   |                      |
|-------------------|----------------------|
| Overview          | Available on Website |
| Wire Guide Tables | Available on Website |

