

Sta-Kon®



Ring Terminal
T&B Catalog Number:

UPC Number:
Status:
Description:

RB14-10X
 78621080415
 Active

Expanded Insulated Nylon Ring Terminal For Wire Range 18-14 Stud Size #10, Blue


WEB_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

Catalog numbers ending with the suffix X indicate an expanded insulation grip. This means a wider wire entry to accommodate heavy wall insulation. Ring terminals won't fall free even if the mounting screw loosens.



General

| | |
|-----------------|--------------------------|
| Insulation Type | Expanded Insulated Nylon |
| Terminal Series | RB |
| Material | Copper |
| Finish | Electro -Tin Plated |
| Color | Blue |
| Wire Range | 18-14 |
| Stud Size | #10 |

Dimension Information

| | |
|-----------------------------|------|
| Maximum Insulation (inches) | .190 |
| Stock Thickness | .03 |
| A (inches) | .95 |
| B (inches) | .31 |
| C (inches) | .25 |
| M (inches) | .79 |

Specifications

| | |
|---------------------|-----------|
| Temperature Rating | 105°C |
| Voltage Rating | 600V |
| Flammability Rating | UL 94 V-2 |

Tooling

| | |
|-------------------|--|
| Tool Charts | Available on Website |
| Application Tools | WT2000, WT112M, WT145C, ERG4001, ERG4003, WT145A |
| Recommended Tool | ERG4001 |

Packaging

| | |
|--------------------|-------------------|
| T&B Order Multiple | 100 |
| T&B Inner Pack | 100 |
| Package in Units | 500 |
| Package Type | Standard |
| T&B Sold in UOM | Each |
| T&B Weight Per UOM | 0.28 lbs. per 100 |