



**Have a Question?**  
Chat with a Product Information Specialist

What can we help you find?

- [Products](#)
- [Industries](#)
- [Resources](#)
- [About TE](#)
- [Support Center](#)
- [My Account](#)

**1520213-4 Product Details**

- [Share](#)
- [Print](#)
- [Email](#)



**Power Toggle Switches**

[Not EU RoHS or ELV Compliant](#)

**Product Highlights:**

- Double Pole - Single Throw Configuration (Pole-Throw)
- Toggle Length = 17.48 mm
- Toggle Style = Baton
- Bushing Length = 11.91 mm
- Termination Type = Screw-In Terminal

[View all Features](#)

**Quick Links**

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

**1520213-4**  
(8910K223)  
TE Internal Number: 1520213-4  
[Active](#)

- [Add to My Part List](#)
- [Request Sample](#)
- [Find Similar Products](#)
- [Buy Product](#)

Documentation & Additional Information	
<p><b>Product Drawings:</b></p> <ul style="list-style-type: none"> <li>• None Available</li> </ul> <p><b>Catalog Pages/Data Sheets:</b></p> <ul style="list-style-type: none"> <li>• None Available</li> </ul> <p><b>Product Specifications:</b></p> <ul style="list-style-type: none"> <li>• None Available</li> </ul> <p><b>Application Specifications:</b></p> <ul style="list-style-type: none"> <li>• None Available</li> </ul> <p><b>Instruction Sheets:</b></p> <ul style="list-style-type: none"> <li>• None Available</li> </ul> <p><b>CAD Files:</b></p> <ul style="list-style-type: none"> <li>• None Available</li> </ul>	<p><b>Related Products:</b></p> <ul style="list-style-type: none"> <li>• <a href="#">Tooling</a></li> </ul>

Product Features (Please use the Product Drawing for all design activity)	
<p><b>Product Type Features:</b></p> <ul style="list-style-type: none"> <li>• Configuration (Pole-Throw) = Double Pole - Single Throw</li> <li>• Termination Type = Screw-In Terminal</li> </ul> <p><b>Electrical Characteristics:</b></p> <ul style="list-style-type: none"> <li>• UL/CSA 125V Current Rating (A) = 16</li> <li>• UL/CSA 250V Current Rating (A) = 8</li> <li>• UL/CSA 125V Horse Power Rating (hp) = 1.00</li> </ul> <p><b>Housing Features:</b></p> <ul style="list-style-type: none"> <li>• Toggle Length (mm [in]) = 17.48 [0.688]</li> <li>• Toggle Style = Baton</li> </ul>	<p><b>Configuration Features:</b></p> <ul style="list-style-type: none"> <li>• Bushing Length (mm [in]) = 11.91 [0.469]</li> </ul> <p><b>Industry Standards:</b></p> <ul style="list-style-type: none"> <li>• <a href="#">RoHS/ELV Compliance</a> = Not ELV/RoHS compliant</li> <li>• <a href="#">Lead Free Solder Processes</a> = Not relevant for lead free process</li> </ul> <p><b>Other:</b></p> <ul style="list-style-type: none"> <li>• Brand = Alcoswitch</li> </ul>

**Corporate Information**

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

**Quick Links**

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

**Customer Support**

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage your Account](#)

**Keep Me Informed**

Receive TE News, Events & Technology Updates

Enter your email address

