



## Terminal Strip,8-Circuit (Box of 10)



### Features

- Torque Rating of 9 in-lbs
- Rugged base eliminates breakage
- Center spacing 0.375" (9.52 mm)
- Accepts #22 to #14 AWG wire
- Corrosion resistant surface plates w/ #6-32 phillslot screws
- Rated to 150V, 20A
- Accessory jumpers available

### Models

Description	Catalog #
Terminal Strip,8-Circuit (Box of 10)	89-308