



B216540

ES FOR LED TRYKK/VRI Ø40 GRØNN

Partnumber: ZB5AW733

Wholesalernumber:

EAN 13 code: 3389110666847

green Ø40 illum mushroom pushbutton head Ø22 latching for integral LED

Technical information

► Compatibility

product compatibility	integral LED
station name	XALD 1 cut-out XALK 1 cut-out

► Functional

type of operator	latching
reset	turn to release
operator profile	green mushroom Ø 40 mm unmarked
electrical composition code	M10 for ≤ 2 contacts using single blocks in front mounting with integral LED M6 for ≤ 2 contacts using single blocks in front mounting with integral LED and transformer MF1 for ≤ 2 contacts using single blocks in front mounting with integral LED MR1 for ≤ 2 contacts using single blocks in rear mounting with integral LED M3 for ≤ 4 contacts using single blocks in front mounting with integral LED M4 for ≤ 4 contacts using single and double blocks in front mounting with integral LED

► Performance

mechanical durability	100000 cycles cycles
-----------------------	----------------------

► Product identification

range of product	Harmony XB5
product or component type	head for illuminated pushbutton
device short name	ZB5
bezel material	plastic
mounting diameter	22 mm mm

► Additional information

sale per indivisible quantity	1
-------------------------------	---

► Physical characteristics

CAD overall width	40 mm mm
CAD overall height	40 mm mm
CAD overall depth	50 mm mm
product weight	0.022 kg kg
resistance to high pressure washer	7000000 Pa at 55 °C, distance: 0.1 m
shape of signaling unit head	round

► Environment

protective treatment	TC
ambient air temperature for storage	-40...70 °C °C
ambient air temperature for operation	-25...70 °C °C
class of protection against electric shock	class II conforming to IEC 60536
IP degree of protection	IP66 conforming to IEC 60529
NEMA degree of protection	NEMA 13 NEMA 4X
IK degree of protection	IK05 conforming to EN 50102
vibration resistance	5 gn (f = 2...500 Hz) conforming to IEC 60068-2-6 30 gn for 18 ms half sine wave acceleration conforming to IEC 60068-2-27
shock resistance	50 gn for 11 ms half sine wave acceleration conforming to IEC 60068-2-27

 **Certifications and standards**

standards

CSA C22-2 No 14
EN/IEC 60947-1
EN/IEC 60947-5-1
EN/IEC 60947-5-4
JIS C 4520
UL 508
GB 14048.5

product certifications

BV
CSA
DNV
GL
LROS (Lloyds register of shipping)
RINA
UL listed

Supplier information

Supplier: Schneider Electric Norge AS

Fax: + 47 64 98 57 01

Web: <http://www.schneider-electric.no>

Adress: Deliveien 10, 1540 Vestby

Phone: +47 64 98 56 00

e-Mail: kundesenter@no.schneider-electric.com