

DUBBELTRYCKE + STOPPKNAPP

**Partnumber:** ZB4BA711137

Wholesalernumber: 3733066

EAN 13 code: 3389119044097

white flush/red projecting/white flush triple-headed pushbutton Ø22 with marking

### Technical information

#### ► Functional

type of operator	spring return
operator profile	2 flush - 1 central projecting STOP pushbuttons
operators description	white "right arrow" - white "left arrow" - red "STOP"
operator profile	red projecting, white STOP white flush, black left arrow white flush, black right arrow
electrical composition code	C1 for <= 9 contacts using single blocks in front mounting C2 for <= 9 contacts using single and double blocks in front mounting C11 for <= 3 contacts using single blocks in front mounting

#### ► Performance

mechanical durability	1000000 cycles cycles
-----------------------	-----------------------

#### ► Product identification

range of product	Harmony XB4
product or component type	head for triple-headed pushbutton
device short name	ZB4
bezel material	black metal
mounting diameter	22 mm mm
colour of marking	black marking when white caps white marking when green, red or black caps

#### ► Additional information

sale per indivisible quantity	1
-------------------------------	---

#### ► Physical characteristics

product weight	0.056 kg kg
resistance to high pressure washer	7000000 Pa at 55 °C,distance: 0.1 m
shape of signaling unit head	rectangular

#### ► Environment

ambient air temperature for storage	-40...70 °C °C
ambient air temperature for operation	-25...70 °C °C
class of protection against electric shock	class I conforming to IEC 60536
IP degree of protection	IP66 conforming to IEC 60529 IP69K conforming to IEC 60529
NEMA degree of protection	NEMA 13 NEMA 4X
IK degree of protection	IK03 conforming to IEC 50102
vibration resistance	5 gn (f = 2...500 Hz) conforming to IEC 60068-2-6 30 gn for 18 ms half sine wave acceleration conforming to IEC 60068-2-27
shock resistance	50 gn for 11 ms half sine wave acceleration conforming to IEC 60068-2-27

#### ► Certifications and standards

standards	CSA C22-2 No 14 EN/IEC 60947-1 EN/IEC 60947-5-1 EN/IEC 60947-5-4 EN/IEC 60947-5-5 JIS C 4520 UL 508
-----------	---

product certifications

BV  
CSA  
DNV  
GL  
LROS (Lloyds register of shipping)  
RINA  
UL listed

**Supplier information**

Supplier: Schneider Electric Sverige AB

Fax: +46 155 26 54 91

Web: <http://www.schneider-electric.se>

Adress: Eskilstunavägen 7, 611 56 Nyköping

Phone: +46 155 26 54 00

e-Mail: [info@se.schneider-electric.com](mailto:info@se.schneider-electric.com)