

Stamped contacts turned crimp female contact for wire gauge 6 - 14

Part No. VN 02 025 0010 (101)

Series Contacts

Subseries Contact Stamped contacts



## COMMON CHARACTERISTICS

|                         |  |                              |
|-------------------------|--|------------------------------|
| Contact diameter        |  | 2,5 mm                       |
| Insulation diameter     |  | 2,5 - 3,5 mm                 |
| Wire gauge from         |  | 1,5                          |
| Wire gauge to           |  | 2,5                          |
| Wire gauge (AWG) from   |  | 16                           |
| Wire gauge (AWG) to     |  | 14                           |
| Packaging / supplied as |  | Single contact               |
| No. of pieces           |  | 100                          |
| Type of contact         |  | Stamped/rolled crimp contact |

## ELECTRICAL CHARACTERISTICS

|                    |  |       |
|--------------------|--|-------|
| Contact resistance | DIN EN 60512-2-1, Test 2a / IEC 60512-2-1, Test 2a | < 5 m |
|--------------------|--|-------|

