


5-Wire Cordsets, Standard Plug Body



- NEMA 1, 3, 4, 6P
- IEC IP68 Protection
- 250 V, 4 A



Connector Style	Female Part Number	Male Part Number	Features	Pinout
<p>RK ..**</p>	RK 4.5T-* WK 4.5T-*	RS 4.5T-* WS 4.5T-*	AWM PVC Grey, 5x22 AWG, 105°C, 5.7 mm OD Cable #RF50543-*M†, flexlife®	<p>Female</p> <p>1. BN 2. WH 3. BU 4. BK 5. GY</p> <p>Male</p> <p>1. BN 2. WH 3. BU 4. BK 5. Drain</p>
<p>WK ..**</p>	RK 4.5T-*/S90 WK 4.5T-*/S90	RS 4.5T-*/S90 WS 4.5T-*/S90	ITC/PLTC TPU Grey, 5x22 AWG, 105°C, 5.7 mm OD, Cable #RF50649-*M†, Cut/Abrasion Immune, tray rated	
<p>RS ..**</p>	RK 4.5T-*/S101 WK 4.5T-*/S101	RS 4.5T-*/S101 WS 4.5T-*/S101	AWM TPE Grey, 5x22 AWG, 105°C, 5.7 mm OD, Cable #RF50909-*M†, flexlife-20, High Flex Over 20 Million Cycles	
<p>WS ..**</p>	RK 4.5T-*/S618 WK 4.5T-*/S618	RS 4.5T-*/S618 WS 4.5T-*/S618	AWM PVC Grey, 5x22 AWG Foil/Drain, 105°C, 5.7 mm OD, Cable #RF50609-*M†, RFI/EMI Protection	
	RK 4.5T-*/S715 WK 4.5T-*/S715	RS 4.5T-*/S715 WS 4.5T-*/S715	AWM PVC Yellow, 5x22 AWG, 105°C, 5.7 mm OD, Cable #RF50684-*M†, flexlife	
	RK 4.5T-*/S653 WK 4.5T-*/S653	RS 4.5T-*/S653 WS 4.5T-*/S653	AWM PVC Grey, 4x22 AWG Foil/Drain, 105°C, 5.1 mm OD, Cable #RF50577-*M†, RFI/EMI Shielding	
	RK 4.5T-*/S1554 WK 4.5T-*/S1554	RS 4.5T-*/S1554 WS 4.5T-*/S1554	AWM PVC Black, 5x22 AWG Foil/Drain, 105°C, 5.7 mm OD, Cable #RF50794-*M†, RFI/EMI Shielding	

Cordsets

* Length in meters. Standard cable lengths are 2, 4, 6, 8 and 10 meters. Consult factory for other lengths.
 ** Standard coupling nut material is nickel plated brass "RK .."; "RKK .." indicates nylon and "RKY .." indicates stainless steel.
 † See Section N for **reelfast**® cable information.