

## GZ10 Spotlights



- Range of spotlights with fully adjustable heads
- Halogen lighting without the need for a transformer
- Pressed steel bases with cast aluminium heads
- Finished in white
- IP20 rated
- Requires GZ10 halogen lamps, max. 50W (not supplied)
- Lamp head  $\varnothing$ : 55mm

Single Spotlight (LxH)	100 x 115mm	Triple Spotlight (Hx $\varnothing$ )	120 x 257mm
Twin Spotlight (LxH)	370 x 120mm		

419414.419294

Description	Order Code	Price Each
<b>Spotlights</b>		
Single Spotlight	<b>108-6737</b>	
Twin Spotlight	<b>108-6738</b>	
Triple Spotlight	<b>108-6739</b>	
<b>240V Halogen Lamps</b>		
GZ10 50W 50°	<b>471-7727</b>	