

## Fluorescent Battens with Tubes



- A range of fluorescent battens with or without prismatic diffusers
- Pressed steel construction
- Tough white stove enamel finish
- Safety rotating lampholders
- Starter switch
- IP20 rated
- BS EN 60598-2-1
- Mail order boxed
- Supplied with branded tubes:
  - 18W: T8 fluorescent 600mm
  - 36W: T8 fluorescent 1200mm
  - 58W: T8 fluorescent 1500mm

419418.419309

Watts	Dims. (LxW)	Order Code	Price Each
<b>Single</b>			
18W	615 x 55mm	<b>108-6752</b>	
36W	1225 x 55mm	<b>108-6754</b>	
58W	1525 x 55mm	<b>108-6755</b>	
<b>Single + Diffuser</b>			
18W	615 x 55mm	<b>108-6756</b>	
36W	1235 x 55mm	<b>108-6757</b>	
58W	1535 x 55mm	<b>108-6758</b>	
<b>Twin + Diffuser</b>			
18W	615 x 125mm	<b>108-6759</b>	
36W	1235 x 125mm	<b>108-6760</b>	
58W	1535 x 125mm	<b>108-6761</b>	