


| CONFIGURATION | PART NUMBER | LENGTH |
|--|--------------|-----------|
| MICROBOSS™ M12, SINGLE ENDED CORDSET, 3 PIN, STRAIGHT FEMALE | MC34AC05Mxxx | SEE BELOW |

DIMENSIONS



TECHNICAL DATA

| | |
|------------------------|--|
| APPROVALS: | UL, c(UL) |
| TEMPERATURE RANGE: | -20C to +105C |
| PROTECTION: | IP 68, NEMA 6P |
| VOLTAGE RATING: | 300V AC & DC |
| AMPERAGE: | 4A |
| HOUSING: | COPPER ALLOY, NICKEL OR BLACK ZINC PLATED |
| CONTACTS: | COPPER ALLOY |
| CONTACT PLATING: | GOLD OVER NICKEL PLATING |
| CONNECTOR FACE: | NYLON 6/6 |
| CABLE CHARACTERISTICS: | 22 AWG WIRE, 300V, PVC JACKET, UL AWM STYLE 2661, CSA AWM I/II A/B |

Sales and Technical Support 1-800-394-7732

www.sineco.com

Amphenol
SINE SYSTEMS