



CONFIGURATION	PART NUMBER	LENGTH
MICROBOSS™ M12, DOUBLE ENDED CORDSET, 4 PIN, FEMALE STRAIGHT / MALE STRAIGHT	MC47A4AC05Mxxx	SEE BELOW

DIMENSIONS



FACE VIEW



FACE VIEW

TECHNICAL DATA

APPROVALS:	UL, c(UL)
TEMPERATURE RANGE:	-20C to +105C
PROTECTION:	IP 68, NEMA 6P
VOLTAGE RATING:	300V AC & DC
AMPERAGE:	4A
HOUSING:	COPPER ALLOY, NICKEL OR BLACK ZINC PLATED
CONTACTS:	COPPER ALLOY
CONTACT PLATING:	GOLD OVER NICKEL PLATING
CONNECTOR FACE:	NYLON 6/6
CABLE CHARACTERISTICS:	22 AWG WIRE, 300V, PVC JACKET, UL AWM STYLE 2661, CSA AWM I/II A/B

Sales and Technical Support 1-800-394-7732

www.sineco.com

Amphenol
SINE SYSTEMS