



CONFIGURATION	PART NUMBER	LENGTH
5 PIN MICRO, FEMALE STR	MC54AC05Mxxx	TBD

DIMENSIONS



WIRING DIAGRAM

BROWN	< 1
WHITE	< 2
BLUE	< 3
BLACK	< 4
GRAY	< 5



FACE VIEW

TOLERANCE	
0-2.99 M	+100.0/-25.0mm
3-8.99 M	+150.0/-25.0mm
9-14.99 M	+300.0/-25.0mm
15-OVER M	+450.0/-25.0mm

TECHNICAL DATA

TEMPERATURE RANGE:	-20C to +105C
PROTECTION:	IP 68, NEMA 6P
VOLTAGE RATING:	300VAC/300VDC
AMPERAGE:	4A
BODY:	OIL RESISTANT PVC
CONTACTS:	COPPER ALLOY
O-RING:	NITRILE RUBBER
CONTACT PLATING:	5 INCHES (MIN) GOLD, OVER 5 INCHES (MIN) NICKEL
CONNECTOR FACE:	NYLON 6/6
COUPLER:	MACHINED ALUMINUM, ANODIZED
CABLE TYPE:	22 AWG, PVC, AWM UL 2661
RECEPTACLE HOUSING:	MACHINED ALUMINUM, ANODIZED

NOTES