


CONFIGURATION	PART NUMBER	LENGTH
5 PIN MICRO, MALE STR	MC57AC05Mxxx	TBD

DIMENSIONS



TECHNICAL DATA

TEMPERATURE RANGE:	-20C to +105C
PROTECTION:	IP 68, NEMA 6P
VOLTAGE RATING:	300VAC/300VDC
AMPERAGE:	4A
BODY:	OIL RESISTANT PVC
CONTACTS:	COPPER ALLOY
O-RING:	NITRILE RUBBER
CONTACT PLATING:	5 INCHES (MIN) GOLD, OVER 5 INCHES (MIN) NICKEL
CONNECTOR FACE:	NYLON 6/6
COUPLER:	MACHINED ALUMINUM, ANODIZED
CABLE TYPE:	22 AWG, PVC, AWM UL 2661
RECEPTACLE HOUSING:	MACHINED ALUMINUM, ANODIZED

NOTES