

H0,75/14D ZH GR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



For the following conductors: 2 No. 0.75 mm² (2 No. AWG 18)

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Order No.	9037410000
Type	H0,75/14D ZH GR
Version	Wire end ferrule, 0.75 mm ² , 8 mm, Colour code: DIN, Grey
GTIN (EAN)	4008190492984
Qty.	500 pc(s).

H0,75/14D ZH GR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions

Length	14 mm	Net weight	0.126 g
--------	-------	------------	---------

Product data

Conductor cross-section	0.75 mm ²	Wire connection cross section AWG, max.	AWG 18
Contact surface length (L2)	8 mm	Collar height (A)	5.5 mm
Collar width (B)	3 mm	Contact surface diameter (D1)	1.7 mm
Metal sleeve thickness (S1)	0.15 mm	Plastic collar thickness (S2)	0.3 mm

Classifications

ETIM 2.0	EC000005	ETIM 3.0	EC000005
UNSPSC	31-16-31-02	eClass 4.1	27-06-07-01
eClass 5.1	27-40-02-01	eClass 6.0	27-40-02-01
eClass 7.0	27-40-02-01		

Product information

Description of article	Twin wire end ferrule, grey
------------------------	-----------------------------

Approvals

Approvals

