

Twist-Lock® Devices


30 Ampere, 125/250 Volts and 3Ø 250 Volts AC

3 Pole, 4 Wire Grounding

Insulgrip® Plugs and Flanged Inlets



30A 125/250V
NEMA L14-30P
UL/CSA
2 (2) HP



30A 3Ø 250V AC
NEMA L15-30P
UL/CSA
3 HP



HBL2711SW




HBL2711S



HBL2711



HBL2715SW



HBL2715

Plugs

Watertight Safety-Shroud®

IP66 SUITABILITY

Description	Cord Dia.	Catalog Numbers
Black Valox® housing, white Valox® clamps.	.35"-1.15" (9-29)	HBL2711SW HBL2721SW

Safety-Shroud

IP20 SUITABILITY

Description	Cord Dia.	Catalog Numbers
Black and white nylon body, white Valox® shroud. Can be used with the Insulgrip Connector Bodies.	.35"-1.15" (9-29)	HBL2711S HBL2721S

Accessories on page B-40.

Insulgrip

IP20 SUITABILITY

Description	Cord Dia.	Catalog Numbers
Black and white nylon.	.35"-1.15" (9-29)	HBL2711 HBL2721
Corrosion resistant, yellow nylon.	.35"-1.15" (9-29)	HBL27CM11 HBL27CM21
All black nylon.	.35"-1.15" (9-29)	HBL2711BK -

Accessories on page B-53.

Flanged Inlets

Watertight Safety-Shroud

IP66 SUITABILITY

Description	Catalog Numbers
Gray Valox® housing and flange.	HBL2715SW HBL2725SW

Accessories on page B-54.

Insulgrip

IP20 SUITABILITY

Description	Catalog Numbers
Nylon casing, back wired.	HBL2715 HBL2725

Accessories on page B-52.

Notes: For technical information on Twist-Lock® and Watertight Safety-Shroud Devices see pages B-69 and 70.



HBLMITL - For use with Watertight Safety-Shroud receptacles, see page B-39.

Valox® is a trademark of SABIC Innovative Plastics, acquired from General Electric Company.