

► **RIBBONS FOR PERMASLEEVE™
WIRE MARKERS**

Recommended for the best performance when printing PermaSleeve markers – before and after shrinkage. Legends on your PermaSleeve markers are resistant to smudging, fading, a variety of chemicals and other harsh environments. Meets the rigid marking requirements of: MIL-I-23053/5 Class 1, MIL-M-81531, MIL-STD-202F, METHOD 215 and UL224.

| Part Number | Description |
|-------------|--|
| R5072 | BLW-3-PS BradyWriter™-III PermaSleeve Printer |
| R5050 | PS-PTR PermaSleeve Printer |
| R5100 | BMXC-PS-PTR BradyMarker™ PermaSleeve Printer |
| R5300 | ID PRO PermaSleeve Printer |
| R5380 | PS-PTR-II PermaSleeve Printer |
| R5390 | SLV-DAT-PTR Printer PermaSleeve and Datab® Printer |

► **SERIES 2000™ RIBBONS FOR
DOT MATRIX PRINTERS**

For legend performance you can't get with an ordinary ribbon, Brady offers the remarkable Series 2000 Ribbon. This fabric ribbon is impregnated with a high-performance indelible ink that dries quickly, won't smear and won't bleed, fade or run when exposed to UV light, weathering or solvents such as 1,1,1-trichloroethane, isopropyl alcohol, Skydrol® 500B and Super Agitene®.

Series 2000 Ribbons come in stock cartridge sizes to fit many IBM, Printronix, Centronix, DEC, Okidata and Epson printers. They are also available as a custom product for use in many other printer cartridges. Regular cleaning of your printer is recommended when using the high-performance Series 2000 Ribbons. See next page for the dot matrix printer cleaning kit.

Skydrol® is a registered trademark of the Monsanto Company. Super Agitene® is a registered trademark of Graymills Corporation.



Ribbon List Series 2000™

| Part Number | Description |
|-------------|---|
| R2001 | C-Itch CI-300 • DEC 6904 • IBM P300, P600, 6408 • Printronix 300P 600, 3000, 6000, 6080, 9000, L150, L600, L9012 • MPV150, MZP3122, P300, P300 BM1717, P300XQ, P6240, P9012 • Series 60 Z-ICOH C1800 • STD Diagnostic P300 Wallace 300 LPM • Weber Legitronic 50/55/60 |
| R2005 | C-Itch 5800 • DEC LA30-36, LA36 • IBM 1443, 2203, 2560, 2780 • ITT 700795-001, Courier 9315 • Texas Instruments 810, 810 in spools • T.I. OMNI 800, 810 • Univac 0798 |
| R2008 | DEC LA120, LA180, LA78 • DIGITAL 120/180 • Digital DECWriter III Genecom 1795 • Texas Instruments 820 • Teleprinter 1000 • T.I. OMNI 800, 810, 820 RO |
| R2012 | Centronics 101 |
| R2020 | Adler SE 1000C • Facit 1850, 1860, 80, 85, 850, 4248 • IBM 82C, TEK 3, Selectric Typewriter, Selectric II 82, 85, 95 • Macintosh Imagewriter • Olympia 6010, 6020, 6510, 6610 • Royal SE 1000C, 6000, 5000C • Triumph Adler |
| R2021 | IBM 5211-1-2-A-B, IBM System 34 Model 1-2, IBM System 38-5211 |
| R2022 | IBM Silver Dollar 3715 |
| R2023 | IBM 3262, 5262, IBM 38-4331/5261, IBM 34-3262 |
| R2024 | IBM Silver Dollar 3287, IBM 38-1-2-3, IBM 5320-A, IBM 535 |
| R2025 | IBM 4207, Proprietary 4201, 4201-001, 4207, 6328829, II • MT4201-002, X-24 4201, X-24 4207 |
| R2050 | BradyPrinter™ PS • Citizen HSP-500, MSP-10, MSP-20, MSP-50 • Epson Action Printer 2000, 2500, T1000, 3210, 810, 8750F, Apex 80 • FX26E, FX80, FX800, FX85, FX850, FX86, FX86E, FX870, GX80 • LX 300, LX400, LX800, LX810, LX850, MX7080, MX80, MX800 • RX80, SX80, T1000 • Hewlett Packard 82905A, 92156A • Honeywell 4/20 • IBM 5125, M1724, Proprietary 5152 • NCR 7052, 7053, 8750 |

| Part Number | Description |
|-------------|--|
| R2051 | Alps 2000, P2000G • Citizen MSP-15, MSP-15E, MSP-45, MSP-55 • DM2015 • Epson 286E, FX100, FX100+, FX105, FX1050, FX185, FX286 • FX286E, FX 1000, FX 1170, LX1000, MX100, MX1000, MX1003, PX100 • RX100, RX1000, SX1050, Action Printer T-750 • Honeywell Italia 4/21, 4/23 • Olympia MP-136, NP36 |
| R2052 | Epson 4000, 510, L1000, LQ400, LQ500, LQ510, LQ550 • LQ800, LQ850, LQ570, LQ870, Action Printer 3000, 4000, 5000, LQ800 • Genicom 20/GP20 |
| R2053 | Citizen 224 • Epson Action Printer 4500,5500,5550,1750 • LQ1000, LQ1010, LQ1050, LQ1070, LQ1070+, LQ 1170, LX1050 |
| R2060 | Apple Imagewriter I, II • AT & T 471, 473, 474, 476, 580 • C-Itch 1550, 1550C, 1550SP 7500, 8500, 8510, 9500, C310, C315, M1550 • Data Products 9030 • DEC 1150, LA50, LA75, LA-75P • IBM 4971, 5533 • Macintosh II • NEC 8023, 8023A, 8025A, LA50 • NCR 6411, 572, 8510 • Telex 281 B/C/D • Toshiba Imagewriter I |
| R2065 | Okidata 120, 80, 80-82, 82, 8283, 82A, 83, 90, 92, 921, 93 • 93+, U83, U92, U93, UAB-3, Star Delta 10, LV1210, LV1215 • SG10, Gemini 10X • Micronics SG-1015 |
| R2070 | BradyWriter™ I |
| R2071 | BradyWriter II (24-pin) • Alps 224E, ALQ-224 • Tandy DMT-2100P • Toshiba 1340, 351, P1340, P1350, P1351, P321, P341, P351 |
| R2072 | BradyWriter II, III • Okidata 292 • Siemens 9011-18, 9011-28 |
| R2080 | IBM 2380, 2381, 2390, 2391, PS-PTR-II, SLV-DAT-PTR |
| R2081 | Okidata 182,192,193,320,321 |
| R2082 | Okidata 520, 521 |
| R2083 | Panasonic KXP 1150/KXP 1695 |
| R2100 | BMCX-Plus |