

## Dremel DSM20-3/4

### Features and benefits

- Excellent visibility of the cutting line for precise cutting.
- Grinding wheel technology for straight cuts, plunge cutting and flush cutting in wood, metal, tiles, plastic and masonry.
- worm gears for durability and performance.
- Powerful 710-watt motor for tough applications.
- Adjustable depth control for precision and control.

• vacuum cleaner attachment for a clean work area. **Contents** •

Dremel DSM20 • 1 x DSM500 multipurpose Karbidtrennscheibe • 3

DSM510 metal and plastic blade • Vacuum adapter • rip fence • 2x4-beam guiding intent • Inspiring Welcome

DVD • Stable and roomy carrying case **Technical data** Rated power input: 710 W Voltage: 220 - 240 V Weight: 1,70 kg No load speed: 17.000 1/min



- **Execution**

- Execution : Set
- Number of revolutions : 17 000 r / min

- **Electrical values**

- Performance : 710 W

- **Connections / Interfaces**

- Connection : 230V

- **Weights**

- Weight : 1.7 kilograms