

SKINDICHT® SM-PE LOCK NUTS

Brass for PG and Metric Threaded Products
Grounding Lock Nuts



SM-PE Lock Nuts are required wherever varnished, anodized and powder coated housings are used. When the lock nut is tightened, it cuts through the insulating

layer guaranteeing optimum contact. Ideal for use with MS-SC cable grounding connectors.



Technical Data:

 Materials: Nickel-Plated Brass

SKINDICHT® SM-PE: PG Brass Lock Nuts

Part Number	Thread Type & Size	Nut Thickness		Wrenching Flats		Standard Pack Size
		inches	mm ²	inches	mm ²	
52103200	PG-7	.185	4.7	.590	15	100
52103210	PG-9	.185	4.7	.709	18	100
52103220	PG-11	.185	4.7	.827	21	100
52103230	PG-13	.185	4.7	.906	23	100
52103240	PG-16	.185	4.7	1.024	26	100
52103250	PG-21	.205	5.2	1.260	32	50
52103260	PG-29	.224	5.7	1.614	41	50
52103270	PG-36	.264	6.7	2.008	51	50

SKINDICHT® SM-PE: Metric Brass Lock Nuts

Part Number	Thread Type & Size	Nut Thickness		Wrenching Flats		Standard Pack Size
		inches	mm ²	inches	mm ²	
52103300	M-12X1.5	.138	3.5	.591	15	100
52103310	M-16X1.5	.138	3.5	.748	19	100
52103320	M-20X1.5	.146	3.7	.945	24	100
52103330	M-25X1.5	.165	4.2	1.181	30	50
52103340	M-32X1.5	.185	4.7	1.417	36	50
52103350	M-40X1.5	.217	5.5	1.811	46	25
52103360	M-50X1.5	.217	5.5	2.362	60	10
52103370	M-63X1.5	.276	7.0	2.756	70	10